

30 Gallon Smart Foam Unit

FI-30N-SM



Features

- Equipped with smart technology.
- Draws from pre-mixed solution.
- Hinged back plate provides tool-free access to components.
- Quick-change pump
- Natural color tank for easy visibility of products
- Hinged lid
- Integrated hose wraps
- Front-facing drain
- In-line strainer to protect from debris
- Anti-kink hose protection
- Includes smart handle extension attachment

Options

- Color coding
 - Lid – 9 colors (BK, BL, BN, GN, OR, PL, RD, WH, YL)

Industries

- Institutional
- Food and beverage
- Manufacturing



how to buy



800 567 5420 | sales@foamit.com

The Good Stuff

- **Smart foam wand**
Automatically depressurizes unit ensuring easier storage and maintenance
- **More control**
The thumb activated wand means users can get a constant stream of foam or “flutter” the nozzle to more precisely apply foam to tricky spots
- **No assembly required**
With integrated hose hangers, this unit is ready to work straight out of the box

Specs

- Power typecompressed air
- Chemical pickup type Draws from pre-mixed solution
- Number of products unit can draw fromOne product
- Capacity 30 gallons (113.6 liters)
- Discharge line length/diameter: 30 ft. (9.1 m) bonded hose, with 5/8 in. (15.9 mm) and 1/4 in. (6.4 mm) inside diameters
- Discharge wand/tip typeultra high molecular weight (UHMW) polyethylene handle and wand, with 65° fan tip and built-in zero tip
- Output distance..... ZERO TIP: 8-12 ft. (2.4-3.7 m)
FAN TIP: 8-12 ft. (2.4-3.7 m)
- Output volume ZERO TIP: 20-32 gal/min (75.7-121.1 l/min)
FAN TIP: 20-32 gal/min (75.7-121.1 l/min)
- Flow rate.....2 gal/min (7.6 l/min)
- Pump seals Santoprene, Viton, or Kalrez
- Wheel type two 10 inch (25.4 cm) non-marking wheels, two 5 inch (12.7 cm) casters, one with lock

Requirements

- Compressed air requirements..... 40-80 psi (2.8-5.5 bar) with 5-10 CFM (141.6-283.2 l/min)
- Liquid temperature range 40-100 °F (4.4-37.8 °C)
- Chemical compatibilitychemical products used with this equipment must be formulated for this type of application and compatible with unit materials and pump seals. For more information on chemical compatibility, consult the manufacturer or SDS for your product or contact our customer service department.