5 Gallon Smart Foam Unit

FI-5N-SM





Features

- · Equipped with smart technology
- · Draws from pre-mixed solution
- · Hinged back plate provides tool-free access to
- Components
- · Quick-change pump
- · Natural color tank for easy visibility of products
- · Hinged lid
- · Integrated hose wraps
- · In-line strainer to protect from debris
- · Anti-kink hose protection
- · Includes smart handle extension attachment

Options

- · Color coding
 - Cap 9 colors (BK, BL, BN, GN, OR, PL, RD, WH, YL)

Industries

- Institutional
- · Food and beverage
- Manufacturing



how to buy



The Good Stuff

Smart foam wand

Automatically depressurizes unit ensuring easier storage and maintenance

More control

The thumb activated wand means users can get a constant stream of foam or "flutter" the nozzle to more precisely apply foam to tricky spots

Configure with color

Caps and hoses come in a variety of colors to match your chemical management systems and quickly tell units apart in your chemical cage

Specs

	•	
	Power type	compressed air
	Chemical pickup typedra	ws from pre-mixed solution
	Number of products unit can draw fro	mone product
	Capacity	5 gallons (18.9 liters)
	Discharge line length/diameter	20 ft. (6.1 m) bonded hose,
		with 5/8 in. (15.9 mm) and
	1/4 ir	. (6.4 mm) inside diameters
	Discharge wand/tip typeultra high	molecular weight (UHMW)
	polyethy	ene handle and wand, with
	65°	fan tip and built-in zero tip
•	Output distance	ZERO TIP: 8-12 ft. (2.4-3.7 m)
		FAN TIP: 8-12 ft. (2.4-3.7 m)
•	Output volumezero TIP: 20)-32 gal/min (75.7-121.1 l/min)
	FAN TIP: 20)-32 gal/min (75.7-121.1 l/min)
•	Flow rate	2 gal/min (7.6 l/min)
•	Pump seals	Santoprene, Viton, or Kalrez
•	Wheel typetwo 4 inch (10	.2 cm) non-marking wheels

Requirements

5-8 cfm (141.6-283.2 l/min)	
Liquid temperature range	
Chemical compatibilitychemical products	
used with this equipment must be formulated for this type of	
application and compatible with unit materials and pump seals. For	
moreinformationonchemicalcompatibility, consultthemanufacturer	
or SDS for your product or contact our customer service department.	