# 10 Gallon Gel Unit

## **GI-10N**





## **Features**

- · Draws from pre-mixed solution
- · Powered by compressed air
- Hinged back plate provides tool-free access to components
- · Quick-change pump
- · Natural color tank for easy visibility of product levels
- · Hinged lid
- Integrated hose wraps
- · In-line strainer to protect pump from debris
- · Front-facing drain
- · Fan tip wand assembly for increased coverage
- · Anti-kink hose protection

# **Options**

- Color coding
  - Lid 9 colors (BK, BL, BN, GN, OR, PL, RD, WH, YL)
  - Discharge hose 4 colors (BL, GN, YL, RD)

# **Industries**

- · Food and beverage
- Manufacturing



how to buy

## The Good Stuff

#### Easy to use, easy to maintain

Designed for portability, efficiency, and hasslefree maintenance. Our quick-change pump and tool-free, hinged access plate reduce downtime when a repair is needed

#### Natural tank

See chemical volume levels at a glance

## Configure with color

Lids and hoses come in a variety of colors to match your chemical management systems and quickly tell units apart in your chemical cage

# **Specs**

Power typecompressed air
Chemical pickup typedraws from pre-mixed solution
Number of products unit can draw fromone product
Suction line diameter
Capacity10 gallons (37.9 liters)
Discharge line length/diameter20 ft. (6.1 m) hose,
with 1/2 in. (12.7 mm) inside diameter
Discharge wand/tip type10 in. (25.4 cm) poly wand
with fan tip and ball valve
(spray tips included: ST1510SS and ST4008SS)
Output distance6-10 ft. (1.8-3 m)
Output volume
Flow rate2 gal/min (7.6 l/min)
Pump sealsSantoprene, Viton, or Kalrez
Wheel typetwo 10 in. (25.4 cm) non-marking wheels

## Requirements

•	Compressed air requirements40-80 psi (2.8-5.5 bar)
	with 2 cfm (56.6 l/min)
	Liquid temperature range40-100°F (4.4-37.8°C)
	Chemical compatibilitychemical products
	used with this equipment must be formulated for this type of
	application and compatible with unit materials and pump seals. For
	moreinformationonchemicalcompatibility, consult themanufacturer
	or SDS for your product or contact our customer service department.