

# Walk-Through Footwear Sanitizing Unit



SS3



## Features

- Users can enter from either side to smooth traffic flow in busy areas
- Walk-through design ensures compliance
- Low-moisture system
- Air-operated pump delivers a consistent amount of sanitizer (0.4 oz/11.8 mL) per spray
- Draws from pre-mixed solution
- Works with our chemical jugs or your chosen chemical reservoir with ¼ in. suction line
- Powered by compressed air
- Easy to disassemble and clean
- Adjustable leveling feet

## Industries

- Institutional
- Food and beverage
- Manufacturing

## The Good Stuff

- **Easy to use**  
Walk through sanitation for entryways and transition zones
- **Easy to clean**  
Collection basin is easy to access or swap out for cleaning
- **Low moisture**  
This unit provides a low moisture cleaning to minimize the spread of disinfecting chemicals and overall humidity

## Specs

- Power type.....compressed air
- Chemical pickup type.....draws from pre-mixed solution
- Number of products unit can draw from.....one product
- Suction line length/diameter ..... 3 ft (0.9 m) clear hose with 1/4 in. (6.4 mm) inside diameter
- Output volume..... 0.4 oz (11.8 mL)
- Flow rate..... 0.4 oz (11.8 mL)
- Pump seals.....Viton
- Number of nozzles..... 8 nozzles
- Product dimensions.....29.5 x 28 x 42 in. (74.9 x 20.3 x 106.7 cm)

## Requirements

- Compressed air requirements.....40-50 psi (2.8-3.4 bar)
- Liquid temperature range ..... 40-100 ° F (4.4-37.8 ° C)
- Chemical compatibility.....chemical products used with this equipment must be formulated for this type of application and compatible with unit materials and pump seals. For more information on chemical compatibility, consult the manufacturer or SDS for your product or contact our customer service department.



how to buy



800 567 5420 | sales@foamit.com