

Airless Walk-Through Footwear Sanitizing Unit



SS5



The Good Stuff

- **Powered by you**
Operated by the force of a human step, this unit is free to go wherever footwear sanitation is needed
- **Consistent coverage**
Eliminates spray bottle applications that result in inconsistent coverage and over-spraying. With four spray tips per side, footwear is evenly and efficiently covered
- **Fast installation, easy serviceability**
Sets up in minutes in any location, no drain required, and is designed for easy maintenance

Features

- Easy-to-use sanitation for entryways and transition zones with no utility installation required
- No compressed air or electricity needed
- Low-moisture system with efficient spray tips for complete coverage
- Draws from pre-mixed solution
- Includes 2.5 gallon jug with suction hose
- Designed for water- or alcohol-based chemistries

Specs

- Power type manual
- Chemical pickup type.....draws from pre-mixed solution
- Number of products unit can draw from.....one product
- Suction line length/diameter.....4 ft. (1.2 m) clear hose with 1/4 in. (96.4 mm) inside diameter
- Output volume0.14 oz. (4.14 mL) per spray, per foot
0.28 oz (8.28 mL) total
- Pump seals..... Viton
- Number of nozzles..... 8 nozzles (4 per foot)

Industries

- Agriculture
- Aviation
- Food and Beverage
- Institutional
- Life Sciences
- Manufacturing
- Remediation

Requirements

- Liquid temperature range.....40-100 ° F (4.4-37.8 ° C)
- Chemical compatibilitychemical products used with this equipment must be formulated for this type of application and compatible with unit materials and pump seals. For more information on chemical compatibility, consult the manufacturer or SDS for your product or contact our customer service department.



How to Buy



800 567 5420 | sales@foamit.com